



Part No. 9000046-XLPDNB External ISM Antenna

868-915 MHz

Supports: IoT, SigFox, LoRa, Cellular LPWA, RPMA, Tracking, Smart Metering, Smart Home, Healthcare, Digital Signage



External European ISM Antenna

868-915 MHz

KEY BENEFITS

Reduced Costs and Time-to-Market

Standard antenna eliminates design fees and cycle time associated with a custom solution; getting products to market faster.

Greater Flexibility with Unique Form Factors

KYOCERA AVX's technology helps you deliver more advanced ergonomic designs without adverse impact on product performance.

RoHS Compliant

Products are the latest RoHS version compliant.

APPLICATIONS

4	ALL LIGATIONS					
•	Medical •	Commercial/				
	applications	Communication				
•	Home •	Radar				
	automation •	Wireless				
•	Smart metering	Monitoring				
•	M2M, Industrial •	Industrial				
	devices •	Automotive				
•	Point of Sale •	Healthcare				
•	Tracking •	IoT				

KYOCERA AVX's family of external antennas are designed to offer the best performances for a wide range of applications. This sleek external antenna covers ISM bands 868 and 915 MHz and specifically provides compelling advantages for ISM enabled handheld devices, media players and other mobile devices.

Global Operations & Design Support

KYOCERA AVX's global operations supports an integrated network of design centers that can take projects from concept to production.

Electrical Specifications

Typical Characteristics on circular 120 mm diameter ground plane

Frequency	868-915 MHz
VSWR	< 2.3:1
Efficiency	70%
Peak Gain	0.9 dBi
Impedance	50 Ω
Polarization	Vertical

Mechanical Specifications & Ordering Part Number

Ordering Part Number	9000046-XLPDNB		
Size (mm)	101.0 ± 3.0 height 11.16 ± 1.0 diameter		
Connector Type	SMA Male		
Weight (grams)	6		
Color	Black		
Operating Temperature (°C)	-40 to +120		





External ISM Antenna Specifications

KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

VSWR, Efficiency, and Peak Gain Plots

Typical Characteristics on circular 120 mm diameter ground plane









External ISM Antenna Specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Antenna Radiation Patterns

Typical Characteristics on circular 120 mm diameter ground plane







DATASHEET | Part No. 9000046-XLPDNB

External ISM Antenna Specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Mechanical Dimensions

Typical antenna dimensions (mm)

Part Number	A (mm)	B (mm)	C (mm)	Connector
9000046-XLPDNB	101.± 3.0	11.16 ± 0.1	8.08 ± 0.1	SMA (Male)

