RF/Microwave Capacitors RF/Microwave Multilayer Capacitors (MLC)

600S Ultra-Low ESR, High Q, NPO Capacitors





APPLICATIONS

- · Cellular Base Stations
- **Broadband Wireless** Services
- Satellite Communications
- Wireless Devices
- WiFi (802.11)
- · Subscriber-based
- · Public Safety Radio

CIRCUIT APPLICATIONS

- · Filter Networks
- High Q Frequency Sources
- Matching Networks
- · Tuning, Coupling, Bypass and DC Blocking

ELECTRICAL SPECIFICATIONS

Capacitance	0.1 to 100 pF
Tolerances	See Cap Value Chart
Working Voltage (WVDC)	250 V
Quality Factor	Greater than 2,000 at 1 MHz (applies to =/> 10pf only)
Operating Temperature Range	-55°C to +125°C (no derating of working voltage)
Temperature Coefficient of Capacitance (TCC)	0 ± 30 ppm/°C, -55°C to +125° $10^5M\Omega$ min. at +25°C at rated WVDC $10^4M\Omega$ min. at +125°C at rated WVDC
Dielectric Withstanding Voltage (DWV)	2.5 x WVDC for 5 seconds
Aging	None
Piezo Effects	None

FEATURES

- · Lowest ESR in Class
- Highest Working Voltage in Class 250 V
- Standard EIA Size: 0603
- · Laser Marking (Optional)
- · High Self-Resonance Frequencies

600 SERIES OVERVIEW

Series	Case Size	EIA Case Size
600	L	0402
600	S	0603
600	F	0805

PACKAGING OPTIONS



Tape & Reel



Tape & Reel





ENVIRONMENTAL CHARACTERISTICS

Themal Shock	5 Cycles, -55°C to 125°C		
Moisture Resistance	Mil-STD-202, Method 106		
Life Test	2000 hours at 125°C at 2X WVDC		
Solderability	Solder Coverage > 90% of end termination		
Terminal Strength	4 lbs. typ., 2 lb. min.		
Military Approval	DSCC Drawing Number 05002		


RF/Microwave Capacitors RF/Microwave Multilayer Capacitors (MLC) 600S Ultra-Low ESR, High Q, NPO Capacitors



CAPACITANCE VALUES

Value (pF)	Cap Code	Marking	Tolerances	Value (pF)	Cap Code	Marking	Tolerances	Value (pF)	Cap Code	Marking	Tolerances
0.1	0R1	A9	A, B	2.7	2R7	L0	A, B, C, D	20	200	H1	F, G, J, K, M
0.2	0R2	H9	A, B	3.0	3R0	M0	A, B, C, D	22	220	J1	F, G, J, K, M
0.3	0R3	M9	A, B, C	3.3	3R3	N0	A, B, C, D	24	240	K1	F, G, J, K, M
0.4	0R4	d9	A, B, C	3.6	3R6	P0	A, B, C, D	27	270	L1	F, G, J, K, M
0.5	0R5	f9	A, B, C	3.9	3R9	Q0	A, B, C, D	30	300	M1	F, G, J, K, M
0.6	0R6	m9	A, B, C	4.3	4R3	R0	A, B, C, D	33	330	N1	F, G, J, K, M
0.7	0R7	n9	A, B, C	4.7	4R7	S0	A, B, C, D	36	360	P1	F, G, J, K, M
0.8	0R8	t9	A, B, C	5.1	5R1	T0	A, B, C, D	39	390	Q1	F, G, J, K, M
0.9	0R9	у9	A, B, C	5.6	5R6	U0	A, B, C, D	43	430	R1	F, G, J, K, M
1.0	1R0	A0	A, B, C, D	6.2	6R2	V0	A, B, C, D	47	470	S1	F, G, J, K, M
1.1	1R1	В0	A, B, C, D	6.8	6R8	W0	B, C, J, K	51	510	T1	F, G, J, K, M
1.2	1R2	C0	A, B, C, D	7.5	7R5	X0	B, C, J, K	56	560	U1	F, G, J, K, M
1.3	1R3	D0	A, B, C, D	8.2	8R2	Y0	B, C, J, K	62	620	V1	F, G, J, K, M
1.5	1R5	E0	A, B, C, D	9.1	9R1	Z0	B, C, J, K	68	680	W1	F, G, J, K, M
1.6	1R6	F0	A, B, C, D	10	100	A1	F, G, J, K, M	75	750	X1	F, G, J, K, M
1.8	1R8	G0	A, B, C, D	11	110	B1	F, G, J, K, M	82	820	Y1	F, G, J, K, M
2.0	2R0	H0	A, B, C, D	12	120	C1	F, G, J, K, M	91	910	Z1	F, G, J, K, M
2.2	2R2	J0	A, B, C, D	15	150	E1	F, G, J, K, M	100	101	A2	F, G, J, K, M
2.4	2R4	K0	A, B, C, D	18	180	G1	F, G, J, K, M				

HOW TO ORDER





The above part number refers to a 600F Series (case size F) 10 pF capacitor, J tolerance (±5%), 250 WVDC, with T termination (Tin Plated over Nickel Barrier, RoHS Compliant), Laser Marking and Tape and Reel packaging.

^{**}Laser Marking is optional


W = Tin/Lead Solder Nickel Barrier














600F Series Data Sheet Condition Description

Capacitors horizontally mounted on 13.3 -mil thick Rogers R0435® softboard 29-mils wide 1/2 oz. Cu traces FSR = lowest frequency at which S11 response, referenced at capacitor edge, crosses real axis on Smith Chart. FPR = lowest frequency at which there is a notch in S21 magnitude response.


RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

600S Ultra-Low ESR, High Q, NPO Capacitors




OUTLINE DIMENSIONS



0 (0(02)	L: .063 ± .006 (1.60 ± 0.15)	T: .035 max (0.89 max)
5 (0603)	L: .063 ± .006 (1.60 ± 0.15) W: .032 ± .006 (.81 ± 0.15)	Y: .014 ± .006 (0.36 ± 0.15)

inches (mm)

SUGGESTED MOUNTING PAD DIMENSIONS



Case Size L, S, and F

Case Size	A Min.	B Min.	C Min.	D Min.			
0402 (1005)	.0275	.0354	.0157	.0866			
	(0.70)	(0.90)	(0.40)	(2.20)			
0603 (1608)	.0393	.0433	.0236	.110			
	(1.00)	(1.10)	(0.60)	(2.80)			
0805 (2012)	.0590	.0512	.0236	.1259			
	(1.50)	(1.30)	(0.60)	(3.20)			

inches (mm)

DESIGN KITS

Kit #	RoHS Compliant	Item #	Description	Cap. Value Range (pF)	Cap. Value (pF)	Tol. (pF)	Price
Kit 25T ROES DK00		DK0025T	600S Series Ultra-low ESR, High Q Microwave Capacitors 16 different values,	0.1 to 2.0	0.1, 0.2, 0.3, 0.4, 0.5, 0.6, 0.7, 0.8,0.9, 1.0, 1.1, 1.2, 1.5	.±0.1%	\$100.00
ROHS	COMPLINE		15 pcs. min. per value		1.6, 1.8, 2.0	.±0.25%	
Kit 26T	A .	DK0026T	600S Series Ultra-low ESR, High Q Microwave Capacitors 16 different values, 15 pcs. min. per value	0.1 to 10	1.0, 1.2, 1.5, 1.8, 2.0. 2.2, 2.4, 2.7, 3.0, 3.3	.±0.1%	
	RoHS				3.9, 4.7, 5.6, 6.8, 8.2	.±0.25%	\$100.00
	COMPLEME				10	.±5%	
Kit 27T	ROHS COMPLEME	DK0027T	600S Series Ultra-low ESR, High Q Microwave Capacitors 16 different values, 15 pcs. min. per value	10 to 100	10, 12, 15, 18, 20, 22, 24, 27, 30, 33, 39, 47 56, 68, 82, 100	.±5%	\$100.00

For Online Kit Orders, Catalog & Application Notes, Visit: www.avx.com