



### GENERAL INFORMATION

KYOCERA AVX offers military approved high frequency BP characteristic (NPO), fixed ceramic chip capacitors in standard EIA sizes. This offering consists of 0402, 0603 and 0805 industry standard case sizes in accordance with DSCC Drawings 05003, 05002 and 05001 respectively. This product is offered in several tested grades. The standard offering is supplied with Group A inspection per MIL-PRF-55681. Additional Group C options are shown below.

### HOW TO ORDER

**05002-**

**Drawing**

**2R0**

**Three Digit Capacitance Code**

The first two digits represent significant figures and the last digit specifies the number of zeros to follow. When fractional values of pF are required, the letter R shall be used to indicate the decimal point.

**B**

**Voltage Code**

**C**

**Capacitance Tolerance Code**

**Z**

**Termination Finish**

Z = Tinned Barrier Termination (Tin/Lead alloy, with a min. of 4% Lead)

**-**

**Group C Option**

Voltage Code Table						
Code	Z	A	B	N	C	K
Rated Voltage (volts, dc)	25	50	100	150	200	250

Tolerance Code Table									
Code	A	B	C	D	F	G	J	K	M
Tolerance	±0.05 pF	±0.1 pF	±0.25 pF	±0.5 pF	±1%	±2%	±5%	±10%	±20%

Group C Option	
Code	Option
C	Full Group C
L	2,000 Hour Life Test Only
M	1,000 Hour Life Test Only
H	Low Voltage Humidity Only
n/a*	No Option

\* (leave position blank)

DSCC DWG. Numbers	EIA Case Size
05003	0402
05002	0603
05001	0805