## **RF/Microwave Capacitors**

RF/Microwave C0G (NP0) Capacitors Ultra Low ESR "U" Series, COG (NP0) Capacitors (RoHS) Automotive, AEC Q200 Qualified, KAQ Series



#### **GENERAL INFORMATION**

Automotive "U" Series capacitors are COG (NP0) chip capacitors specially designed for "Ultra" low ESR for applications in the automotive market. Max ESR and effective capacitance are met on each value producing lot to lot uniformity. Sizes available are EIA chip sizes 0402 and 0603.

#### **DIMENSIONS:** inches (millimeters)



inches (mm)

Size	Α	В	С	D	E
0402	0.039±0.004 (1.00±0.1)	0.020±0.004 (0.50±0.1)	0.024 max (0.6)	N/A	N/A
0603	0.060±0.010 (1.52±0.25)	0.030±0.010 (0.76±0.25)	0.036 max (0.91)	0.010±0.005 (0.25±0.13)	0.030 min (0.76)

#### **HOW TO ORDER**











1H

Capacitance Code Code (in pF) 2 Significant Digits +Number of zeros eg.  $10\mu F = 106$ 

9R1





Tolerance  $B = \pm 0.1 pF$  $C = \pm 0.25 \, pF$ 

 $D = \pm 0.50 pF$  $F = \pm 1\% (>= 10 pF)$  $G = \pm 2\% (>= 10 pF)$ 

 $J = \pm 5\%$ K = ± 10%  $M = \pm 20\%$ 



Code	EIA (inch)	IEC(mm)	7" Paper	7" Embossed	13" Paper	13"Embossed
05	0402	1005	Н		N	
15	0603	1608	T		М	





**Packaging** 

See Table Below

### **HOW TO ORDER**

#### **ELECTRICAL CHARACTERISTICS**

## **Capacitance Values and Tolerances:**

Size 0402 - 0.2 pF to 22 pF @ 1 MHz Size 0603 - 1.0 pF to 100 pF @ 1 MHz

#### **Temperature Coefficient of Capacitance (TC):**

0±30 ppm/°C (-55° to +125°C)

#### Insulation Resistance (IR):

 $10^{12}\,\Omega$  min. @  $25^{\circ}$ C and rated WVDC  $10^{11} \Omega$  min. @  $125^{\circ}$ C and rated WVDC

### Working Voltage (WVDC):

Size Working Voltage 0402 - 100, 50, 25 WVDC 0603 - 200, 100, 50 WVDC

#### Dielectric Working Voltage (DWV):

250% of rated WVDC

#### **Equivalent Series Resistance Typical (ESR):**

0402 See Performance Curve, page 303 0603 See Performance Curve, page 303

#### **Automotive Specifications**

Meets or exceeds the requirements of AEC Q200

# **RF/Microwave Capacitors**

## RF/Microwave C0G (NP0) Capacitors Ultra Low ESR "U" Series, COG (NP0) Capacitors (RoHS) Automotive, AEC Q200 Qualified, KAQ Series



## **CAPACITANCE RANGE**

SIZE		0402	0603			
Soldering		All Paper	All Paper			
(L) Length mm		1.00± 0.10	1.60 ±0.15			
(in.)		(0.040± 0.004)	(0.063±0.006)			
(W) Width		0.50 ±0.10	0.81±0.15			
	(in.)	(0.020 ±0.004)	(0.032±0.006)			
(t) Terminal	mm	0.25±0.15	0.35±0.15			
**	(in.)		0.010±0.006) (0.014±0.006)			
WVDC		50	50	100	200	
Cap	0.2	A	A	Α	A	
(pF)	0.3	A	Α	Α	Α	
	0.4	A	A	Α	A	
	0.5	A	A	Α	A	
	0.6	A	A	Α	A	
	0.7	A	A	Α	A	
	0.8	A	A	Α	A	
	0.9	A	A	Α	Α	
	1.0	A	A	A	A	
	1.1	A	A	A	A	
	1.2	A	A	A	A	
	1.3	A	A	A	A	
	1.4	A	A	Α	A	
	1.5	A	A	Α	A	
	1.6	A	A	Α	А	
	1.7	A	Α	Α	Α	
	1.8	A	Α	Α	Α	
	1.9	A	A	Α	A	
	2.0	A	A	Α	A	
2.1		A	Α	Α	Α	
	2.2	A	A	Α	A	
2.4		A	A	Α	A	
	2.7	A	A	Α	A	
	3.0	A	Α	Α	Α	
	3.3	A	A	Α	A	
	3.6	A	A	Α	A	
	3.9	A	A	Α	A	
	4.3	A	A	A	A	
	4.7	A	A	A	A	
	5.1	A	A	A	A	
	5.6	A	A	A	A	
	6.2	A	A	A	A	
	6.8	A	A	A	A	
	7.5	A A	A	A	A	
	8.2		A	A	A	
	9.1	A	A	A	A	
10		A	A	A	A	
11		A	A	A	A	
12		A	A	A	A	
13		A	A	A	A	
15		A	A	A	A	
18		A	A	A	A	
20		A	A	A	A	
22		A	A	A	A	
24		A	A	A	A	
27		A	A	A	A	
Cap	30	A	A	A 100	A 200	
WVDC		50	50	100	200	
SIZE		0402		0603		

0.75		0.400		0.00		
SIZE		0402	0603			
Soldering		All Paper	All Paper			
(L) Length	mm	1.00± 0.10	1.60 ±0.15			
., -	(in.)	(0.040± 0.004)	(0.063±0.006)			
(W) Width	mm	0.50 ±0.10	0.81±0.15			
. ,	(in.)	(0.020 ±0.004)	(0.032±0.006)			
(t) Terminal	mm	0.25±0.15		0.35±0.15		
	(in.)	(0.010±0.006)		(0.014±0.006)		
WVDC		50	50	100	200	
(pF)	33	A	Α	Α	Α	
	36	A	A	A	A	
	39	A	A	A	A	
	43		A	A	A	
	47		A	A	A	
	51		A	A	A	
	56		A	A	A	
	68		A	A	Α	
	75		Α	Α		
	82		Α	Α		
	91		Α	Α		
	100		Α	Α		
110						
120						
130						
140						
150						
160						
	180					
	200					
	220					
	270					
	300					
	330					
	360					
390						
430						
470						
510						
560						
620						
680						
750						
820						
910						
1000						
WVDC		50	50	100	200	
SIZE		0402		0603		

Case Size	0402 (KAQ05)	0603 (KAQ15)	
Thickness Letter	Α	Α	
Max Thickness(mm)	0.55	0.90	
Carrier Tape	PAPER	PAPER	
Packaging Code 7"reel	Н	T	
Packaging Code 13"reel	N	М	
	PAI	PER	

## **TOLERANCE OPTIONS**


Capacitance Range	Available Tolerances
0.20-0.50 pF	B, C
0.60-6.2 pF	B,C, D
6.8- 9.1 pF	B, C, J, K, M
10-1000 pF	F,G, J, K, M

# **RF/Microwave Capacitors**

RF/Microwave C0G (NP0) Capacitors Ultra Low ESR "U" Series, COG (NP0) Capacitors (RoHS) Automotive, AEC Q200 Qualified, KAQ Series



**ULTRA LOW ESR, "U" SERIES** 



## **TYPICAL ESR vs. FREQUENCY** 0603 "U" SERIES 3.9 pF -5.1 pF -6.8 pF ESR (ohms) 10.0 pF 0.01 2500 500 1000 1500 2000

Frequency (MHz)

**SERIES RESONANT FREQUENCY** "U" SERIES CHIP -0402 0603 Frequency (GHz) Capacitance (pF)

**TYPICAL**