

Oven Controlled Crystal Oscillator

9 x 14mm Standard OCXO – Family Data Sheet



FEATURES

- Stratum 3E Compliant
- Thru Hole or Surface Mountable
- High Stability vs. Temperature
- Quick Warm-Up Time
- Low Age Rates
- Low Phase Noise
- 9 x 14mm Package

KYOCERA AVX's high performance OCXO product offering is a result of 90+ years of leading products within the Frequency Control Industry. Modern layout topologies enable KYOCERA AVX to engineer and manufacture robust designs for all applications.



HOW TO ORDER

KAVX Standard OCXO Series

Mounting
 T: Through Hole
 S: SMT
P Package = 9mm x 14mm

Center Frequency
 10M: MHz to
 120M: MHz
MHz

Supply Voltage
 D: 3.3V
 E: 5V
EFC
 N: N/A
 A: ±0.5ppm
 B: ±1ppm

Notes:
 - Configuration items are in blue
 - Not all combinations of options may be possible
 - Other options may be available

Shipping
 B: Bulk
 T: Tape & Reel

Output Type
 A: Sine
 C: CMOS/TTL

Operating Range
 A: 0 to 70°C
 B: -20 to 70°C
 C: -40 to 85°C
 H: -40 to 75°C


Frequency vs. Temperature
 B: ±5ppb
 C: ±10ppb
 D: ±20ppb
 E: ±50ppb
 F: ±100ppb

Configuration Code: K O V S P 40 M D N C C A T

APPLICATIONS

- Network Infrastructure
- 5G Picocell
- Test and Measurement Systems
- GPS Precision Timing Devices
- Medical Devices
- Aerospace
- Industrial

BLOCK DIAGRAM



Note: If EFC Option "N" is used, connect V_{EFC} to GND



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order

Oven Controlled Crystal Oscillator

9 x 14mm Standard OCXO – Family Data Sheet



PERFORMANCE SPECIFICATIONS

Parameter	Conditions	Values			Unit
		MIN	TYP	MAX	
Frequency Range		10		120	MHz
Initial Tolerance	@ +25°C (Nominal)			±100	ppb
Warm Up Time	To initial tolerance			3	Min
Frequency Stability					
vs. Temperature	Options B - (Max-Min)/2		±5		ppb
	Options C - (Max-Min)/2		±10		ppb
	Options D - (Max-Min)/2		±20		ppb
	Options E - (Max-Min)/2		±50		ppb
	Options F - (Max-Min)/2		±100		ppb
vs. Load	± 5% Δ in Load		±2		ppb
vs. Supply Voltage	± 5% Δ in supply		±2		ppb
ADEV (Short Term Stability)	T = 1 second		5E-11		
Aging					
Per Day	After 30 Days Operation			±1.0	ppb
				±100	ppb
Supply Voltage (Vdd)	Option D	3.13	3.3	3.47	Vdc
	Option E	4.75	5	5.25	Vdc
Power Dissipation					
Start Up	@ +25°C (Nominal)			2.5	W
Steady State	@ +25°C (Nominal)		0.9		W
Electronic Frequency Control					
Voltage Range		0	Vdd/2	Vdd	Vdc
Frequency Range	Option N	0			ppm
	Option A	±0.5			ppm
	Option B	±1.0			ppm
Slope			positive		
Input Impedance			100		kΩ
Linearity			10		%

Note: Values typical of 10MHz units



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order

Oven Controlled Crystal Oscillator

9 x 14mm Standard OCXO – Family Data Sheet



PERFORMANCE SPECIFICATIONS

Parameter	Conditions	Values			Unit
		MIN	TYP	MAX	
Output Characteristics (CMOS/TTL)					
High Output Level	Logic "1"	90% Vdd			Vdc
Low Output Level	Logic "0"	10% Vdd			Vdc
Rise/Fall Time		5			nSec
Duty Cycle		45	50	55	%
Load		15			pF
Output Characteristics (Sinusoid)					
Output Level		9.0			dBm
Spurious		-70			dBc
Harmonics		-40			dBc
Load		45	50	55	Ω

Parameter	Conditions	Values		Unit
		TYP	TYP	
Phase Noise				
Phase Noise (10 MHz)	Tested at +25°C (Nominal)	Sinusoid	CMOS	
	10Hz	-120	-120	dBc/Hz
	100Hz	-140	-140	dBc/Hz
	1kHz	-145	-145	dBc/Hz
	10kHz	-155	-150	dBc/Hz
	100kHz	-155	-155	dBc/Hz
Phase Noise (100 MHz)	Tested at +25°C (Nominal)	Sinusoid	CMOS	
	10Hz	-90	-90	dBc/Hz
	100Hz	-120	-120	dBc/Hz
	1kHz	-145	-140	dBc/Hz
	10kHz	-155	-145	dBc/Hz
	100kHz	-155	-150	dBc/Hz

Note: Values typical of 10MHz units



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order

Oven Controlled Crystal Oscillator

9 x 14mm Standard OCXO – Family Data Sheet



ENVIRONMENTAL COMPLIANCE

Parameter	Conditions	Values			Unit
		MIIN	TYP	MAX	
Operating Temperature	Option A	0		+70	°C
	Option B	-20		+70	°C
	Option C	-40		+85	°C
Storage Temperature		-55		+100	°C
Seal	MIL-STD-202 Method 112 Test Condition D				
Mechanical Shock	MIL-STD-202, Method 213, Test Condition C				
Vibration	Mil-Std-202, Method 201				
Acceleration Sensitivity	10MHz output Vibration profile: 0.001G ² /Hz 10Hz to 2kHz		1.0		ppb/g
Stratum 3E	Holdover at 25 °C	-10		+10	ppb




The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order

Oven Controlled Crystal Oscillator


9 x 14mm Standard OCXO – Family Data Sheet



ACCEPTABLE REFLOW PROFILE



TAPE AND REEL



Tape Dimensions (mm)								Reel Dimensions (mm)	
W	F	Do	Po	P1	P2	B1	T2	Outside Dia.	Parts / Reel
32	14.5	1.5	4.0	20	2.0	14.4	11.8	330	250

Notes:

1. Profile Classification per IPC/JEDEC J-STD-020C Pb-Free Small Body Assembly
2. Only the SMT version can be selected as a Tape & Reel shipping method
3. If Tape & Reel is required a MOQ of 200-piece increments are required.







The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order

Oven Controlled Crystal Oscillator


9 x 14mm Standard OCXO – Family Data Sheet



MECHANICAL SPECIFICATIONS – SURFACE MOUNT



MARKING



Tolerances (mm) .X = ± 0.5, .XX = ± 0.2 unless otherwise specified

PIN	FUNCTION
1	EFC / N.C.
2, 5	N.C.
3	Ground
4	RF Output
6	Supply Voltage



- Notes:
- Non-RoHS available upon request



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order