0402/0603 Low Capacitance Multilayer Varistors **ESD Protection for Antennas and Low Capacitor Loading Applications**




GENERAL DESCRIPTION

KYOCERA AVX 0402/0603 AntennaGuard products are an ultra-low capacitance extension of the proven TransGuard® TVS (transient voltage suppression) line of multilayer varistors. RF designers now have a single chip option over conventional protection methods (passive filters with diode clamps), which not only gives superior performance over traditional schemes, but also provides the added benefits of reduced PCB real estate and lower installation costs.

KYOCERA AVX AntennaGuard products are available in capacitance ratings of ≤3pF (0402 & 0603 chips), 2 and 12pF (0603 chip). These low capacitance values have low insertion loss, as well as give other TransGuard® advantages such as small size, subnanosecond response time, low leakage currents and unsurpassed reliability (FIT Rate of 0.2) compared to diodes.

RF antenna/RF amplifier protection against ESD events is a growing concern of RF circuit designers today, given the combination of increased signal "gain" demands, coupled with the required downsizing of the transistor package. The ability to achieve both objectives is tied to a reduced thickness of the SiO2 gate insulator layer within the semiconductor. The corresponding result of such a change increases the Power Amplifier's (PA's) vulnerability to ESD strikes - a common event with handheld electronic products with RF transmitting and/or receiving features. KYOCERA AVX Low Capacitance AG Series parts are ideal solution for this type of applications as well as for many more where low capacitance ESD protection is needed.



GENERAL CHARACTERISTICS

- Operating Temperature: -55°C to +125°C
- Working Voltage: ≤18Vdc
- Case Size: 0402, 0603

FEATURES

- Smallest TVS Component
- Single Chip Solution
- Low Insertion Loss
- · Fastest Response Time to ESD Strikes
- · Capacitance: 2, 3 and 12pF

APPLICATIONS

- **RF** Amplifiers
- **Antennas**
- **Laser Drivers**
- Sensors
- Radars
- **RFID**
- Keyless entry
- Near fileld communication
- **Datalines**
- Capacitance sensitive applications and more

HOW TO ORDER



Chip Size 04 = 0402

04

06 = 0603

Varistor Series AntennaGuard

AG

Working Voltage (DC)

3R0 18

Capacitance 2pF = 2R0 3pF = 3R0 12pF = 120

Υ Non-Std. Cap Tolerance $C = \pm 0.25 pF (2R0)$ Y = Max (3R0)

Y = +4, -2pF (120)

Not

Applicable

Capacitance T = Ni/Sn (Plated)

Size 1 = 7'3 = 13 W = 7'

(0402 only)

X Reel **Ouantity** A = 4.000or 10,000 (i.e., 1A = 4,000)

3A = 10.000WA = 10,000





0402/0603 Low Capacitance Multilayer Varistors **ESD Protection for Antennas and Low Capacitor Loading Applications**

ANTENNAGUARD CATALOG PART NUMBERS/ELECTRICAL VALUES

Part Number	VW (DC)	VW (AC)	IL	Сар	Cap Tolerance	Case Size
VC04AG183R0YAT	≤ 18	≤ 14	0.1	3	Max	0402
VC06AG182R0CAT	≤ 18	≤ 14	0.1	2	±0.25pF	0603
VC06AG183R0YAT	≤ 18	≤ 14	0.1	3	Max	0603
VC06AG18120YAT	≤ 18	≤ 14	0.1	12	+4, -2pF	0603


L Termination Finish Code - Packaging Code

 V_w (DC) DC Working Voltage (V) V_w (AC) AC Working Voltage (V)

Maximum Leakage Current at the Working Voltage (µA)


Maximum Capacitance (pF) @ 1 MHz and 0.5 Vrms; VC06AG18120YAT capacitance tolerance: +4, -2pF Cap

PHYSICAL DIMENSIONS



Size (EIA)	Length (L)	Width (W)	Max Thickness (T)	Land Length (t)
0402	1.00±0.10	0.50±0.10	0.60	0.25±0.15
	(0.040±0.004)	(0.020±0.004)	(0.024)	(0.010±0.006)
0603	1.60±0.15	0.80±0.15	0.90	0.35±0.15
	(0.063±0.006)	(0.031±0.006)	(0.035)	(0.014±0.006)

SOLDERING PAD DIMENSIONS



mm (inches)

mm (inches)

Suppression	Pad Dimensions					
Device	Α	В	С	D		
0402	1.70 (0.067)	0.61 (0.024)	0.51 (0.020)	0.61 (0.024)		
0603	2.54 (0.100)	0.89 (0.035)	0.76 (0.030)	0.89 (0.035)		

0402/0603 Low Capacitance Multilayer Varistors **ESD Protection for Antennas and Low Capacitor Loading Applications**



ANTENNA VARISTORS

KYOCERA AVX offers a series of 0402 and 0603 chip varistors, designated the AntennaGuard series, for RF antenna/RF amplifier protection. These devices offer ultra-low capacitance (<3pF in 0402 chips, and ≤3pF & ≤12pF in 0603 packages), as well as low insertion loss. Antenna varistors can replace output capacitors and provide ESD suppression in RF and capacitance sensitive applications.

It is very common to employ some form of a FET in many types of efficient/ miniature RF amplifiers. Typically, these RF transistors have nearly ideal input gate impedance and outstanding noise figures. However, FETs are very susceptible to ESD damage due to the very thin layer of SiO2 uses as the gate insulator. The ultra-thin SiO2 layer is required to improve the gain of the transistor. In other words, the upside of the performance enhancement becomes the downside of the transistors survival when subjected to an FSD event.

ESD damage to the RF Field Effect Transistors (FETs) is a growing concern

among RF designers due to the following trends: (1) RF amplifiers continue to shrink in size, and (2) FET gains figures continue to increase. Both trends relate to decreasing gate oxide thickness, which in turn, is directly proportional to increased ESD sensitivity. As miniaturization trends accelerate, the traditional methods to protect against ESD damage (i.e., PC board layout, passive filters, and diode clamps) are becoming less and less effective.

KYOCERA AVX AntennaGuard varistor can be used to protect the FET and offer superior performance to the previously mentioned protection methods given above. The standard EIA 0603 chip size, and particularly the 0402 chip, offer designers an ESD protection solution consistent with today's downsizing trend in portable electronic products. Savings in component volume up to 86%, and PC board footprint savings up to 83% are realistic expectations. These percentages are based upon the following table and Figures 1A and 1B.

mm (inches)

	Pad Dimensions					
Suppression Device	D1	D2	D3	D4	D5	
0402 TransGuard®	1.70 (0.067)	0.61 (0.024)	0.51 (0.020)	0.61 (0.024)	0.51 (0.020)	
0603 TransGuard®	2.54 (0.100)	0.89 (0.035)	0.76 (0.030)	0.89 (0.035)	0.76 (0.030)	
Competitor's SOT23 Diode	See Below					




Figure 1A. 0402/0603 IR Solder Pad Layout




Figure 1B. SOT23- Solder Pad Layout

0402/0603 Low Capacitance Multilayer Varistors **ESD Protection for Antennas and Low Capacitor Loading Applications**



Antenna varistors offer excellent ESD repetitive strike capability compared to a SOT23 diode when subjected to IEC 61000-4-2 8Kv contact discharge. A performance summary is shown in Figure 2.

ESD TEST OF ANTENNAGUARD RATINGS





Figure 2. Repetitive 8kV ESD Strike

Antenna varistors also turn on and divert ESD overvoltages at a much faster rate than SOT23 devices (typically 300pS vs 1500pS - 5000pS). See Figure 3.



The equivalent circuit model for a typical antenna varistor is shown in Figure




Figure 4. Antenna Varistor

The varistor shown exhibits a capacitance of ≤3pF which can be used to replace the parallel capacitance typically found prior to the antenna output of an RF amplifier. In the off state, the varistor acts as a capacitor and helps to filter RF output. The varistor is not affected by RF output power or voltage and has little insertion loss. See Figure 3.

ANTENNA VARISTOR S21




Figure 5. Antenna vs Frequency

Typical implementations of the antenna varistors are shown for use in cell phone, pager and wireless LAN applications in Figures 6A, 6B and 6C.




Figure 6A. Cell Phone




Figure 6B. Pager




Figure 6C.

