

# Part No. 1005194 UWB PCB Antenna with SMA Connector

6.0 - 8.5 GHz

Supports: Smart Home, Agriculture, Tracking, Radar, Automotive, Healthcare, Digital Signage, Telematics



**UWB PCB Embedded Antenna** 

KYOCERA AVX's 1005194 is a versatile off-board UWB PCB antenna optimized for applications spanning 6.0 – 8.5 GHz where off-board implementation is advantageous and necessary. The 1005194 antenna incorporates a rigid mounting structure through an SMA connection allowing for ease of assembly to any device.

### **Electrical Specifications**

Typical Performance using antenna with SMA connector in Free-space.

Frequency	6.0 – 8.5 GHz			
Peak Gain	6.1 dBi			
Average Efficiency	85%			
VSWR Match	2.0 :1 max			
Feed Point Impedance	50 ohms unbalanced			
Polarization	Linear			
Operation Temperature	-40 to +85 °C			
Power Handling	10 Watt			

# KEY BENEFITS

### Stay-in-Tune

6000 - 8500 MHz

KYOCERA AVX antenna technology provides superior RF field containment, resulting in less interaction with surrounding components.

#### **Quicker Time-to-Market**

By optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily met.

#### Reliability

Products are the latest RoHS version compliant

## **APPLICATIONS**

Embedded design
 Radar
 Gateway, Access Point
 Healthcare M2M, Industrial devices
 Smart Grid

OBD-II

- HandheldTelematics
- Tracking

# **Mechanical Specifications & Ordering Part Number**

Ordering Part #	1005194				
Dimensions (mm)	20.6 x 18.6 x 0.8				
Weight (grams)	2.7 ~ 4.3				
Connector (mm)	SMA compatible connector				
Mounting	Screw Mount				
Storage Temperature (°C)	-40 to +85				
Packaging	PE bags				


<sup>\*</sup>Additional variations available with different connectors.




**UWB PCB antenna with SMA connector Specifications** KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.


# Typical VSWR, Efficiency and Peak Gain plots


Typical Performance using antenna with SMA connector in Free-space.





1005194









UWB PCB antenna with SMA connector Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

#### **Radiation Patterns Plots**

Typical Performance using antenna with SMA connector in Free-space. Typical Performance @ 6500, 7000, 8000 MHZ










UWB PCB antenna with SMA connector Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.


#### **Mechanical Dimensions**

Typical antenna dimensions (mm)

Part Number	A (mm)	B (mm)	C (mm)	D (mm)	*Connector Type
1005194-A01	20.6 ± 0.2	18.6 ± 0.2	8.0	31.5	SMA Male
1005194-B02	20.6 ± 0.2	18.6 ± 0.2	0.8	27.5	SMA Female


<sup>\*</sup>Additional variations available with different connectors.





\_C\_\_\_\_

**Side View** 



**Top View**