
RF/Microwave Multilayer Capacitors (MLC)

550-560 Series UBC™ Ultra-Broadband Capacitor





GENERAL DESCRIPTION

KYOCERA AVX new Ultra-Broadband Capacitor is manufactured with highest quality materials to provide reliable and repeatable Ultra-Broadband performance from 7KHz through 110GHz. It exhibits ultra-low insertion loss, flat frequency response and excellent return loss, and is ideal for D.C. Blocking, Coupling, Bypassing and Feedback applications requiring Ultra-Broadband performance.

TYPICAL CIRCUIT APPLICATIONS

- · Optoelectronics/High Speed Data
- Transimpedance amplifiers
- Receive and Transmit Optical Sub-Assembly (ROSA/TOSA)
- Synchronous Optical Network (SONET)
- · Broadband test equipment
- Broadband Microwave/Millimeter Wave

ADVANTAGES

- · Ultra-Broadband performance
- · Ultra-Low Insertion Loss
- Flat Frequency Response
- Excellent Return Loss
- Unit-to-Unit Performance Repeatability
- Rugged Ceramic Construction
- Operating Temperature: -55°C to +125°C Note: See voltage below on the table at certain temp.

HOW TO ORDER





Capacitance Code EIA Capacitance Code in pF. First two digits = significant figures or "R" for decimal place. Third digit = number of zeros or after "R" significant figures



 $M = \pm 20\%$ P = +100%, -0% V = +20%, -10% Y = +25%, -20%



Termination Style Code T = Tin Plated over Nickel Barrier (Standard) CA = Gold Plated over Nickel Barrier



Tape & Reel



Packaging T = 1000 pc qty.T/500 = 500 pc qtyT/4k = 4000 pc qty. Z = 15K pc for 0201 20kpc for 01005

Т

ELECTRICAL SPECIFICATIONS

Series	Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish	Packaging
550W103M	01005	160kHz	110GHz	10	35	25	16	Tin	
560W103M	01005	160kHz	50GHz	10	35	25	16	Tin	
550W104M	01005	16kHz	110GHz	100	6.3	4		Tin	
560W104M	01005	16kHz	40GHz	100	6.3	4		Tin	T 7
560Z104M	0201	16kHz	40GHz	100	25	16	6.3	Tin	T, Z
550Z104M	0201	16kHz	110GHz	100	25	16	6.3	Tin	
560Z224M	0201	7.2kHz	40GHz	220	16	10	4	Tin	
550Z224M	0201	7.2kHz	70GHz	220	16	10	4	Tin	
550Z103M	0201	160kHz	100GHz	10	10	10	6.3	Tin/Gold	Т
560L104Y	0402	16kHz	40GHz	100	16	16	16	Tin	T/500
550L104K	0402	16kHz	70GHz	100	16	16	16	Tin/Gold	T/4K



502

Click on part number to see performance data and download files


RF/Microwave Multilayer Capacitors (MLC)

550-560 Series UBC™ Ultra-Broadband Capacitor



GENERAL DIMENSIONS


		550W104	560W104	560Z104	560Z224	560L104
L	mm	0.40 ± 0.02	0.40 ± 0.02	0.60 ± 0.03	0.60 ± 0.03	1.0 ± 0.1
(Length)	(in)	(0.016 ± 0.0008)	(0.016 ± 0.0008)	(0.024 ± 0.001)	(0.024 ± 0.001)	(0.040 ± 0.004)
W	mm	0.20 ± 0.02	0.20 ± 0.02	0.30 ± 0.03	0.30 ± 0.03	0.5 ± 0.1
(Width)	(in)	(0.008 ± 0.0008)	(0.008 ± 0.0008)	(0.012 ± 0.001)	(0.012 ± 0.001)	(0.020 ± 0.004)
Т	mm	0.22 Max	0.22 Max	0.22 Max	0.33 Max	0.6 Max
(Thickness)	(in)	0.009 Max	0.009 Max	0.009 Max	0.013 Max	0.024 Max
t	mm	0.135 ± 0.035	0.135 ± 0.035	0.15 ± 0.05	0.15 ± 0.05	0.36 ± 0.08
(Terminal)	(in)	(0.005 ± 0.0014)	(0.005 ± 0.0014)	(0.006 ± 0.002)	(0.006 ± 0.002)	(0.014 ± 0.003)



		550W103	560W103	550Z103	550Z104	550Z224	550L104
L	mm	0.40 ± 0.02	0.40 ± 0.02	0.58 ± 0.03	0.60 ± 0.03	0.60 ± 0.03	1.0 ± 0.1
(Length)	(in)	(0.016 ± 0.0008)	(0.016 ± 0.0008)	(0.023 ± 0.001)	(0.024 ± 0.001)	(0.024 ± 0.001)	(0.040 ± 0.004)
W	mm	0.20 ± 0.02	0.20 ± 0.02	0.32 ± 0.03	0.30 ± 0.03	0.30 ± 0.03	0.5 ± 0.1
(Width)	(in)	(0.008 ± 0.0008)	(0.008 ± 0.0008)	(0.0125 ± 0.0010)	(0.012 ± 0.001)	(0.012 ± 0.001)	(0.020 ± 0.004)
Т	mm	0.2 Max	0.2 Max	0.35 Max	0.22 Max	0.33 Max	0.6 Max
(Thickness)	(in)	0.008 Max	0.008 Max	0.013 Max	0.009 Max	0.013 Max	0.024 Max
+ (Tarminal)	mm	0.135 ± 0.035	0.135 ± 0.035	0.20 ± 0.04	0.23 ± 0.05	0.23 ± 0.05	0.42 ± 0.08
t (Terminal)	(in)	(0.005 ± 0.0014)	(0.005 ± 0.0014)	(0.008 ± 0.0015)	(0.009 ± 0.002)	(0.009 ± 0.002)	(0.0165 ± 0.0030)

REFLOW SOLDERING

560		01005	0201	0402		
а	mm	0.10 - 0.15	0.20 - 0.25	0.40 - 0.60		
a	(in)	(0.004 - 0.006)	(0.008 - 0.010)	(0.016 - 0.024)		
b	mm	0.13 - 0.19	0.25- 0.35	0.40 - 0.50		
ь	(in)	(0.005 - 0.007)	(0.010 - 0.014)	(0.016 - 0.020)		
С	mm	0.20 - 0.23	0.30 - 0.40	0.50 - 0.75		
C	(in)	(0.008 - 0.009)	(0.012 - 0.016)	(0.020 - 0.030)		
550		01005	0201	0402		
	mm	0.10 - 0.15	0.10 - 0.15	0.15 - 0.20		
а	mm (in)	0.10 - 0.15 (0.004 - 0.006)	0.10 - 0.15 (0.004 - 0.006)	0.15 - 0.20 (0.006 - 0.008)		
a b	(in)	(0.004 - 0.006)	(0.004 - 0.006)	(0.006 - 0.008)		
	(in)	(0.004 - 0.006)	(0.004 - 0.006) 0.30 - 0.40	(0.006 - 0.008) 0.50 - 0.62		



Parts are sensitive to orientation. Maintain packaging orientation for typical performance.

RF/Microwave Multilayer Capacitors (MLC)

550-560 Series UBC™ Ultra-Broadband Capacitor



Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
01005	160kHz	110GHz	10	35	25	16	Tin




*Data files contain DXF and S2P files

Click here to return to main table

PERFORMANCE DATA





550W Data Sheet Test Condition Description


All testing performed on 5-mil-thick Rogers RO3003 board using recommended footprint. (nominal 50-ohm characteristic impedance) @ Modelithics.


560W103M

Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
01005	160kHz	50GHz	10	35	25	16	Tin
						Click here to re	eturn to main table

PERFORMANCE DATA

Series Insertion Loss (S21) Series Return Loss (S11)





560W Data Sheet Test Condition Description

All testing performed on 10-mil-thick Rogers RO3006 microstrip board, with the device under test subtending a 4 mil gap in a 14.2-mil-wide center trace (nominal 50-ohm characteristic impedance).

RF/Microwave Multilayer Capacitors (MLC)

550-560 Series UBC™ Ultra-Broadband Capacitor




Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
01005	16kHz	110GHz	100	6.3	4	-	Tin

PERFORMANCE DATA

Click here to return to main table





550W Data Sheet Test Condition Description

All testing performed on 5-mil-thick Rogers R03003 board using recommended footprint. (nominal 50-ohm characteristic impedance) @ Modelithics.


560W104M

Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
01005	16kHz	40GHz	100	6.3	4		Tin


PERFORMANCE DATA

Series Return Loss (S11)

Click here to return to main table



Series Insertion Loss (S21)



560W Data Sheet Test Condition Description

All testing performed on 10-mil-thick Rogers RO3006 microstrip board, with the device under test subtending a 4 mil gap in a 14.2-mil-wide center trace (nominal 50-ohm characteristic impedance).

RF/Microwave Multilayer Capacitors (MLC)

550-560 Series UBC™ Ultra-Broadband Capacitor



Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
0201	16kHz	40GHz	100	25	16	6.3	Tin




*Data files contain DXF and S2P files

Click here to return to main table

Click here to return to main table

PERFORMANCE DATA





560Z Data Sheet Test Condition Description

All testing performed on 5-mil-thick Rogers RO3003 board using recommended footprint. (nominal 50-ohm characteristic impedance) @ Modelithics.

550Z104M


Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
0201	16kHz	110GHz	100	25	16	6.3	Tin



*Data files contain DXF and S2P files

PERFORMANCE DATA





550Z Data Sheet Test Condition Description

All testing performed on 5-mil-thick Rogers RO3003 board using recommended footprint. (nominal 50-ohm characteristic impedance) @ Modelithics.

RF/Microwave Multilayer Capacitors (MLC)

550-560 Series UBC™ Ultra-Broadband Capacitor



560Z224M


Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
0201	7.2kHz	40GHz	220	16	10	4	Tin



*Data files contain DXF and S2P files Click here to return to main table

PERFORMANCE DATA





560Z Data Sheet Test Condition Description

All testing performed on 5-mil-thick Rogers RO3003 board using recommended footprint. (nominal 50-ohm characteristic impedance) @ Modelithics.


550Z224M

	Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
	0201	7.2kHz	70GHz	220	16	10	4	Tin
Click here to return to mai								



*Data files contain DXF and S2P files

PERFORMANCE DATA





550Z Data Sheet Test Condition Description

All testing performed on 5-mil-thick Rogers RO3003 board using recommended footprint. (nominal 50-ohm characteristic impedance) @ Modelithics.

RF/Microwave Multilayer Capacitors (MLC)

550-560 Series UBC™ Ultra-Broadband Capacitor




550Z103P


Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
0201	160kHz	100GHz	10	10	10	6.3	Tin/Gold



*Data files contain DXF and S2P files Click here to return to main table

PERFORMANCE DATA





550Z Data Sheet Test Condition Description


All testing performed on 5-mil-thick Rogers RO3003 board using recommended footprint. (nominal 50-ohm characteristic impedance) @ Modelithics.


560L104Y

Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
0402	16kHz	40 GHz	100	16	16	16	Tin/Gold

PERFORMANCE DATA

Click here to return to main table





560L Data Sheet Test Condition Description

All testing performed on 10 mil-thick rogers RO4350B microstrip board, with the device under test subtending a 24 mil gap in a 22 mil-wide center trace (nominal 50 ohms characteristic impedance).

RF/Microwave Multilayer Capacitors (MLC)

550-560 Series UBC™ Ultra-Broadband Capacitor



550L104K


Size (EIA)	Min Frequency	Max Frequency	Cap (nF)	WVDC (85C)	WVDC (105C)	WVDC (125C)	Finish
0402	16kHz	70GHz	100	16	16	16	Tin/Gold




Click here to return to main table *Data files contain DXF and S2P files

PERFORMANCE DATA







550L Data Sheet Condition Description

All testing performed on 10 mil-thick rogers RO4350B microstrip board, with the device under test subtending a 24 mil gap in a 22 mil-wide center trace (nominal 50 ohms characteristic impedance).

SIMULATION MODELS



KYOCERA AVX and Modelithics have partnered to offer FREE 90-Day trials of highly accurate, scalable advanced simulation models for various KYOCERA AVX parts including THIS part as well as Attenuators, Capacitors, Couplers, Inductors, Diplexers, Resistors.

For More Information, Please Visit: https://www.modelithics.com/mvp/avx Use Promo Code: AVXWP