High Capacitance Tantalum Solid Electrolytic Chip Capacitors Undertab Series





FEATURES

- · Large Case Size for Maximum Capacitance
- 3x Reflow 260°C Compatible
- 100% Surge Current Tested
- · Low Profile Solution
- **Consumer Applications** (e.g. PCMCIA/USB Wireless Express Cards etc.)
- CV Range: 1000-3300µF / 4-10V
- · 2 Case Sizes Available

APPLICATIONS

- · Data Transfer Modems
- · SSD Backup Circuits






CASE DIMENSIONS:


millimeters (inches)

| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H max. | W _P ±0.10 (0.004) | W _N ±0.10 (0.004) | A _P ±0.10 (0.004) | A _N ±0.10 (0.004) | S Min. |
|------|-------------|---------------|-------------------|---------------------------------|--------------|---------------------------------|---------------------------------|---------------------------------|---------------------------------|--------------|
| 4 | 2924 | 7361-20 | 7.30 (0.287) | 6.10 (0.240) | 2.00 (0.079) | 4.75 (0.187) | 4.75 (0.187) | 2.00 (0.079) | 3.20 (0.126) | 2.10 (0.083) |
| 6 | 5831 | 14878-20 | 14.80 (0.583) | 7.80 (0.307) | 2.00 (0.079) | 5.50 (0.217) | 5.50 (0.217) | 2.45 (0.096) | 2.45 (0.096) | 9.90 (0.390) |


MARKING


4,6 CASE





HOW TO ORDER







006 **Rated DC Voltage** 004 = 4Vdc006 = 6.3 Vdc010 = 10 Vdc



Packaging R = Pure Tin 7" Reel



ESR in mΩ

TECHNICAL SPECIFICATIONS

| Technical Data: | All technical data relate to an ambient temperature of +25°C | | | | | | | | |
|------------------------------------|--|----------|--|-----------|--------------|--|--|--|--|
| Capacitance Range: | 1000 μF to 3300 μF | | | | | | | | |
| Capacitance Tolerance: | | | ±20% | | | | | | |
| Leakage Current DCL: | | 0.01CV | | | | | | | |
| Rated Voltage (V _R) | -55°C ≤ +40°C: | 4 | 6.3 | 10 | | | | | |
| Category Voltage (V _c) | at 85°C: | 2 | 3.2 | 5 | | | | | |
| Category Voltage (V _c) | at 125°C: | 0.8 | 1.3 | 2 | | | | | |
| Temperature Range: | | -55°C to | +125°C v | vith cate | gory voltage | | | | |
| Reliability: | | | 0.2% per 1000 hours at 85° C, $0.5xV_R$ with $0.1\Omega/V$ series impedance with 60% confidence level | | | | | | |

102020





CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

| Capac | itance | Voltage Rating DC (VR) to 85°C | | | | | | | |
|-------|--------|--------------------------------|----------|--------------|--|--|--|--|--|
| μF | Code | 4V (G) | 6.3V (J) | 10V (A) | | | | | |
| 680 | 687 | | | | | | | | |
| 1000 | 108 | | | 4(100)/6(55) | | | | | |
| 1500 | 158 | | 4(100) | 6(55) | | | | | |
| 2200 | 228 | | 6(55) | | | | | | |
| 3300 | 338 | 6(55) | | | | | | | |

Released ratings (ESR ratings in mOhms in parentheses)

Note: Voltage ratings are minimum values. KYOCERA AVX reserves the right to supply higher voltage ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

| | Case | Capacitance | Rated | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (µA) | ESR Max. @ 100kHz (mΩ) | 100kHz RMS Current (mA) | | | |
|------------------|-----------------|-------------|----------------|------------------------------|----------------------------|---------------------------------|---------------------|---------------------------------|-------------------------|------|-------|-----|
| Part Number | Size | (μF) | Voltage (V) | | | | | | 25°C | 85°C | 125°C | MSL |
| 4 Volt @ 40°C | | | | | | | | | | | | |
| TLN6338M004#0055 | 6 | 3300 | 4 | 40 | 0.8 | 125 | 132 | 55 | 2045 | 1840 | 818 | 3 |
| | 6.3 Volt @ 40°C | | | | | | | | | | | |
| TLN4158M006#0100 | 4 | 1500 | 6.3 | 40 | 1.3 | 125 | 90 | 100 | 1285 | 1156 | 514 | 3 |
| TLN6228M006#0055 | 6 | 2200 | 6.3 | 40 | 1.3 | 125 | 132 | 55 | 2045 | 1840 | 818 | 3 |
| | 10 Volt @ 40°C | | | | | | | | | | | |
| TLN4108M010#0100 | 4 | 1000 | 10 | 40 | 2 | 125 | 100 | 100 | 1285 | 1156 | 514 | 3 |
| TLN6108M010#0055 | 6 | 1000 | 10 | 40 | 2 | 125 | 100 | 55 | 2045 | 1840 | 818 | 3 |
| TLN6158M010#0055 | 6 | 1500 | 10 | 40 | 2 | 125 | 150 | 55 | 2045 | 1840 | 818 | 3 |

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts.

DCL is measured at rated voltage after 5 minutes.

ESR allowed to move up to 1.25 times catalogue limit post mounting

DCL allowed to move up to 2.00 times catalogue limit post mounting

For typical weight and composition see page 259.

NOTE: KYOCERA AVX reserves the right to supply higher voltage ratings or tighter tolerance part in the same case size, to the same reliability standards.


High Capacitance Tantalum Solid Electrolytic Chip Capacitors Undertab Series



QUALIFICATION TABLE

| TEST | TLN PulseCap™ series (Temperature range -55°C to +125°C) | | | | | | | | | | | |
|---------------------------------------|--|------------------------|---------------------|-------------------------------|---------------------------------|-----------------------------|---------|------------|--|----------|--|--|
| 1531 | | Condition | Characteristics | | | | | | | | | |
| | Apply rated voltage | ge (Ur) at 40°C and | Visual examination | examination no visible damage | | | | | | | | |
| Endurance | ''' / | 5°C for 2000 hours | DCL | 2 x initia | 2 x initial limit | | | | | | | |
| Endurance | | .1Ω/V. Stabilize at re | ΔC/C | within + | within +5/-30% of initial value | | | | | | | |
| | for 1-2 hours befo | ore measuring. | ESR | 1.25 x ir | 1.25 x initial limit | | | | | | | |
| | Store at 65°C and | d 90-95% relative hu | Visual examination | no visib | no visible damage | | | | | | | |
| Llumaiditu | | plied voltage. Stabi | DCL | 2 x initia | 2 x initial limit | | | | | | | |
| Humidity | | humidity for 1-2 ho | ΔC/C | within ± | within ±10% of initial value | | | | | | | |
| | measuring. | | | ESR | 1.25 x ir | nitial limit | | | 0 x IL* 25 x IL* 2 x IL* 0/-0% +25/-0% ±10% | | | |
| | Step 1 | Temperature°C +20 | Duration(min) 15 | _ | +20°C | -55°C | +20°C | +85°C | +125°C | +20°C | | |
| Temperature | 2 | -55 | 15 | DCL | 2 x IL* | n/a | 2 x IL* | 20 x IL* | 25 x IL* | 2 x IL* | | |
| Stability | 3 | +20 +85 | 15 15 | ΔC/C | n/a | +5/-20% | ±10% | +20/-0% | +25/-0% | +10% | | |
| · · · · · · · · · · · · · · · · · · · | 5 | +125 | 15 | ESR | 1.25xIL* | | - | | | - | | |
| | 6 | +20 | 15 | - | | | | 1.25 X IL^ | 1.25 X IL^ | 1.25XIL^ | | |
| | | voltage (Ur) at 40°C | | Visual examination | | no visible damage | | | | | | |
| Surge | | (30 sec charge, 5 r | DCL | | 2 x initial limit | | | | | | | |
| Voltage | of 1000Ω | gh a charge / discha | ΔC/C | | within ±5% of initial value | | | | | | | |
| | 01 100002 | | | ESR | | nitial limit | | | 0 x IL* 25 x IL* 2 x IL* 20/-0% +25/-0% ±10% | | | |
| | | | | Visual examination | no visible damage | | | | | | | |
| Mechanical | | | DCL | | initial limit | | | | | | | |
| Shock | MIL-STD-202, Me | thod 213, Condition | ΔC/C | | within ±5% of initial value | | | | | | | |
| | | | | DF | | initial limit | | | | | | |
| | | | | ESR | | initial limit | | | | | | |
| | | | | Visual examination | | no visible damage | | | | | | |
| | | | | DCL | initial limit | | | | | | | |
| Vibration | MIL-STD-202, Method 204, Condition D | | | ΔC/C | | within ±5% of initial value | | | | | | |
| | | | | DF | initial lir | initial limit | | | | | | |
| | | | | ESR | initial lir | initial limit | | | | | | |

^{*}Initial Limit




040120

High Capacitance Tantalum Solid Electrolytic Chip Capacitors Undertab Series



SOLID ELECTROLYTIC CAPACITOR ROADMAP



FIVE CAPACITOR CONSTRUCTION STYLES



SERIES LINE UP: CONVENTIONAL SMD MnO.

