

Part No. 1004112

Broadband External LTE / Cellular Antenna

700 / 750 / 850 / 900 / 1800 / 1900 / 2100 / 2700 MHz

Supports: Broadband LTE (OCTA-BAND), LTE CAT-M, NB-IoT, SigFox, LoRa, Cellular LPWA, RPMA



KYOCERA AVX 1004112 antenna is designed to offer the best performances across LTE frequencies, regardless of the ground it is connected to. Its hinged connector and low profile design allows for diverse integration and functionality. Please refer to ordering guide for connector selection.

The 1004112 broadband antenna offers full coverage for LTE bands 2, 4, 5, 7, 8, 12, 13, 14, 17, 25, 26 among others. KYOCERA AVX antennas are versatile easy plug and play solutions for any major network carriers.

High Performance External LTE/Cellular Antenna

Low Band : 698-960 MHz

High Band: 1710-2155 MHz

High High Band: 2500-2700 MHz

KEY BENEFITS

Greater Flexibility

Different connector options upon request. Small form factor and low profile. Independent of ground, the performances are maintained across design.

Quicker Time-to-Market

Standard antenna eliminates design fees, redesign cycle time and minimize risk associated with a customer solution. Quicker time to market.

Environmental Compliance

Comply with latest RoHS requirements

APPLICATIONS

- Medical applications
- Home automation
- Smart metering
- M2M, Industrial devices
- IoT
- Firstnet
- Healthcare (FDA Class I)
- Point of Sale
- Tracking
- NB-IoT
- Sigfox
- LoRa
- Cellular LPWA
- RPMA
- LTE CAT-M

Electrical Specifications

Measured in Free space

Frequency (MHz)	690-960	1710-2200	2500-2700
VSWR Match	< 2.5:1	< 2.5:1	< 2.5:1
Average Efficiency	65%	60%	78%
Peak Gain	1.18 dBi	4.5 dBi	4.0 dBi
Polarization	Linear		
Feed Point Impedance	50 Ω unbalanced		

Mechanical Specifications & Ordering Part Number

Ordering Part #	1004112-A001	1004112-B002	1004112-C003
Dimensions (mm)	218.2 x 27.2 x 13.8	227.1 x 27.2 x 14.5	218.2 x 27.2 x 13.8
Mounting Type	External	External	External
Connector Type	SMA (MALE) 90° Hinged	TNC (MALE) 90° Hinged	SMA (MALE) 90° Hinged
Antenna Color	White	Black	Black
Weight (grams)	31.5	43.2	31.5
Operating Temperature (°C)	-30 to +70		
Max Power Handling (W)	5		
Additional Resources	Download 3D FIT File		


*Additional variations available in different colors and connectors

External LTE / Cellular KYOCERA AVX Embedded Antenna Specifications.
 KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.


VSWR and Efficiency

Typical performance, measured in free space


Low Band VSWR




Low Band Efficiency




High Band VSWR




High Band Efficiency



High High Band VSWR




High High Band Efficiency




External LTE / Cellular KYOCERA AVX Embedded Antenna Specifications.
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.


Antenna Radiation Patterns – Low / High Band
Typical performance, measured in free space



Low Band measured at 750 MHz




High Band measured at 1720 MHz




External LTE / Cellular KYOCERA AVX Embedded Antenna Specifications.
 KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Antenna Radiation Patterns – High High Band

Typical performance, measured in free space



High High Band measured at 2550 MHz




External LTE / Cellular KYOCERA AVX Embedded Antenna Specifications.
 KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Mechanical Dimensions

Typical antenna dimensions (mm)

Part Number	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)	G (mm)	Connector
1004112-A001	218.2 ± 3.0	27.2 ± 1.0	13.8 ± 1.0	10.1 ± 0.5	197.4 ± 3.0	27.4 ± 2.0	41.5 ± 2.0	SMA (Male)
1004112-B002	227.1 ± 3.0	27.2 ± 1.0	13.8 ± 1.0	14.5 ± 0.5	197.4 ± 3.0	36.4 ± 2.0	50.0 ± 2.0	TNC (Male)
1004112-C003	218.2 ± 3.0	27.2 ± 1.0	13.8 ± 1.0	10.1 ± 0.5	197.4 ± 3.0	27.4 ± 2.0	41.5 ± 2.0	SMA (Male)



External LTE / Cellular KYOCERA AVX Embedded Antenna Specifications.
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Additional Resources – 1004112

3D FIT File:

https://www.kyocera-avx.com/download/antennas/ME-FIT/1004112_ME_fit.zip