




DATASHEET Part No. 1004292PT Product: Wi-Fi Tunable PCB 5 GHz Embedded Antenna

Part No. 1004292PT Wi-Fi Tunable PCB 5 GHz Embedded Antenna

5 GHz

Supports: Wi-Fi applications, Agriculture, Automotive, Bluetooth, Zigbee, WLAN, Smart Home, Healthcare, Digital Signage



PCB Wi-Fi Tunable Embedded Antenna with Cable

5.150 - 5.825 GHz

KEY BENEFITS

Stay-in-Tune

KYOCERA AVX antenna technology provides superior RF field containment, resulting in less interaction with surrounding components.

Quicker Time-to-Market

By optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily met.

Reliability

Products are the latest RoHS version compliant

APPLICATIONS

- Embedded
 Telematics
 design
 Tracking
- design Tracking • Cellular, • Healthcare Headsets, • M2M,
 - TabletsIndustrialGateway,devicesAccess PointSmart Grid
- Handheld OBD-II

KYOCERA AVX 1004292PT is a versatile off-board PCB antenna ideal for 5 GHz Wi-Fi applications where off-board implementation is advantageous and necessary. 1004292PT is ideal for systems requiring a multiple antenna solution.

1004292PT offers easy on-the-go tuning capability right on the antenna face, that is ideal for prototyping. The tuned antenna can then be hardwired by KYOCERA AVX for mass production. Standard connector options available: U.FL and MHF4L.

Custom cable and connector options are available. Please contact us for more information.

Electrical Specifications

Typical Performance using 100 mm cable tested on PC-ABS

Frequency	5.150 – 5.825 GHz
Peak Gain	4.8 dBi
Average Efficiency	70%
VSWR Match	2.0 :1 max
Feed Point Impedance	50 ohms unbalanced
Polarization	Linear
Power Handling	2 Watt CW

Mechanical Specifications & Ordering Part Number

Ordering Part #	1004292PT-AA10L0100
Dimensions (mm)	22.0 x 8.0 x 0.4
Weight (grams)	0.9
Cable/ Connector (mm)	Length: 100, Diameter: 1.13, Color: Black; U.FL compatible connector (MHF4L options available)
Mounting	Adhesive on bottom side of antenna
Packaging	PE bags


*Additional variations available with different cable lengths, colors and connectors.

Proprietary





Typical VSWR, Efficiency and Peak Gain plots

Measured in free space with PC/ABS loading and 100 mm cable













Radiation Patterns Plots

Measured with PC/ABS loading and 100 mm cable Typical Performance @ 5200 MHZ



Antenna Tuning Procedure


This antenna has unique features enabling limited range RF tuning by solder bridging or cutting specified area. Ease of tuning for any application on the fly with a soldering iron and knife. Tuning optional if required.



Antenna Tuning (High)







<u>Cut Gap</u>




Antenna Tuning

This antenna has unique features enabling limited range RF tuning by solder bridging or cutting specified area. Ease of tuning for any application on the fly with a soldering iron and knife.


Antenna Tuning Structure



*Solder bridge between pads for frequency tuning



*Cut Pads for frequency tuning







KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.









	Stage	Pads	Frequency Shift (MHz)	
	Stage 1 (Baseline)	DNI	N/A	
	Stage 2	P1	-134	
	Stage 3	P1+P2	-190	
OLIFE	Stage 4	P3	-27	
Shift Low	Stage 5	P3+P4	-62	
	Stage 6	P3+P4+P5	-109	
	Stage 7	P6+P7+P8	-29	
	Stage 8	C1	17	
	Stage 9	C2	32	
<u>Shift High</u>	Stage 10	C3	36	
	Stage 11	C4	107	
	Stage 12	C5	222	









Stage 5

Ш



1004292PT

WI ANA





© 2021 KYOCERA AVX

1004292P

WI ANA

tel +(1) 858.550.3820 email: <u>eth.info@KYOCERA-AVX.com</u>




Tuning Options (High)


Stages 8-12 (Tuning antenna "High" applying cut on designated area)




*Ex: Tune Frequency Higher Apply Cut to designated stage for optimal tuning.





	Stage	Pads	Frequency Shift (MHz)		
	Stage 1 (Baseline)	DNI	N/A		
	Stage 2	P1	-134		
	Stage 3	P1+P2	-190		
0.1711	Stage 4	P3	-27		
Shift Low	Stage 5	P3+P4	-62		
	Stage 6	P3+P4+P5	-109		
	Stage 7	P6+P7+P8	-29		
	Stage 8	C1	17		
<u>Shift High</u>	Stage 9	C2	32		
	Stage 10	C3	36		
	Stage 11	C4	107		
	Stage 12	C5	222		





*Measured in free space with PC/ABS loading and 100 mm cable





Stage 12

1004292PT

WI ANA

Stage 10



Stage 11 1004292P WI ANA

© 2021 KYOCERA AVX




Mechanical Dimensions (U.FL compatible)

Typical antenna dimensions mm


Dimensions in () parenthesis are Reference Only.

Part Number	А	В	С	D	Connector compatibility	Connector orientation
1004292PT-AA10L0025	(22.0)	(8.0)	(0.4)	25.0 ± 3.0	U.FL	Face Down
1004292PT-AA10L0050	(22.0)	(8.0)	(0.4)	50.0 ± 3.0	U.FL	Face Down
1004292PT-AA10L0075	(22.0)	(8.0)	(0.4)	75.0 ± 3.0	U.FL	Face Down
1004292PT-AA10L0100	(22.0)	(8.0)	(0.4)	100.0 ± 3.0	U.FL	Face Down
1004292PT-AA10L0150	(22.0)	(8.0)	(0.4)	150.0 ± 4.0	U.FL	Face Down
1004292PT-AA10L0200	(22.0)	(8.0)	(0.4)	200.0 ± 4.0	U.FL	Face Down

*Total Height of 1.8 mm includes the cable solder connection Thickness of 0.4 mm includes PCB + adhesive thicknesses *Connector shown in photo below is "Face Down"



Side View






Mechanical Dimensions (MHF4L compatible)

Typical antenna dimensions mm


Dimensions in () parenthesis are Reference Only.

Part Number	А	В	С	D	Connector	Connector orientation
1004292PT-AC10L0025	(22.0)	(8.0)	(0.4)	25.0 ± 3.0	MHF4L	Face Down
1004292PT-AC10L0050	(22.0)	(8.0)	(0.4)	50.0 ± 3.0	MHF4L	Face Down
1004292PT-AC10L0075	(22.0)	(8.0)	(0.4)	75.0 ± 3.0	MHF4L	Face Down
1004292PT-AC10L0100	(22.0)	(8.0)	(0.4)	100.0 ± 3.0	MHF4L	Face Down
1004292PT-AC10L0150	(22.0)	(8.0)	(0.4)	150.0 ± 4.0	MHF4L	Face Down
1004292PT-AC10L0200	(22.0)	(8.0)	(0.4)	200.0 ± 4.0	MHF4L	Face Down

*Total Height of 1.8 mm includes the cable solder connection Thickness of 0.4 mm includes PCB + adhesive thicknesses *Connector shown in photo below is "Face Down"



Side View



Bottom View

