
Chip Tantalum Capacitors (Large Capacitance)





FEATURES

- Ta-MnO₂ technology
- Low DCL
- Parameters stability over voltage and time
- Undertab and J-lead LF








APPLICATIONS

- DC/DC
- Industrial
- Telecom
- IoT
- Home applications
- Sensors

MARKING







CASE DIMENSIONS:

Code	EIA EIA Code Metric		L±0.10 (0.004)			W ₁ ±0.10 (0.004)	A±0.10 (0.004)
М	0603	1608-09	1.60 (0.063)	0.85 (0.033)	0.80 (0.031)	0.55 (0.022)	0.50 (0.020)


CASE DIMENSIONS:

millimeters (inches)

millimeters (inches)

Code	EIA Code			W±0.20 (0.008)	H±0.20 (0.008)	W ₁ ±0.20 (0.008)	A±0.30 (0.012)	
Α	1206	3216-18	3.20 (0.126)	1.60 (0.063)	1.60 (0.063)	1.20 (0.047)	0.80 (0.031)	
Р	0805	2012-12	2.00 (0.079)	1.25 (0.049)	1.20 (0.047) max.	0.90 (0.035)	0.45 (0.018)	

HOW TO ORDER





0J

Rated DC Voltage 0G = 4Vdc 0J = 6.3Vdc 1A = 10Vdc 1C = 16Vdc 1D = 20Vdc 1E = 25Vdc

475

Capacitance Code pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)

M **Tolerance**

 $K = \pm 10\%$ $M = \pm 20\%$

8R Packaging 8 = Tape width

R = Positive electrode on the side opposite to sprocket hole



Discrimination code





TECHNICAL SPECIFICATIONS

Technical Data:	All technical data relate to an ambient temperature of +25°C	
Capacitance Range:	0.15μF to 100μF	
Capacitance Tolerance:	±20%	
Leakage Current DCL:	Please see the ratings and part number reference table below	
Temperature Range:	-55°C to +125°C	

Note: Conductive Polymer Capacitors are designed to operate within the limits of the environmental conditions specified for each series. If operated continuously at their maximum temperature and / or humidity limit, or beyond these limits, capacitors may exhibit a parametric shift in capacitance and increases in ESR. These changes may occur earlier if the specified environmental conditions are exceeded. Similarly, their normal operational time period will be significantly extended if their general duty cycle includes operation below maximum temperature within humidity controlled environments. Careful attention should be paid to maximum temperature with associated high humidity environments as well as voltage derating, ripple current and current surges.

Please reference the KYOCERA AVX Conductive Polymer Capacitor Guidelines for more information or contact factory for application assistance

CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capacitance			Ra	ated Voltage	DC (V _R) @ 8	5°C			Сар
μF	Code	4V (g)	6.3V (j)	10V (A)	16V (C)	20V(D)	25V(E)	50V(H)	Code
0.15	154							Α	<u>E</u>
1.0	105			Р	A,M,P	Α	A,M,P		Α
1.5	155				Α				E
2.2	225		Р	A,M,P	A,M				J
3.3	335			A,P	Α		Α		N
4.7	475		A,M,P	A,M,P	Α	Α	Α		S
6.8	685		Р	Α	Α				W
10	106	A,M,P	A,M,P	A*,M,P	A*				а
15	156		Р	Α					е
22	226	A,M, P	A,M,P	Α	Α				j
33	336	Α	A,M	Α					n
47	476	Α	Α						S
68	686	Α							w
100	107	Α							ā

Released ratings (*K tolerance is also available)

Note: Voltage ratings are minimum values. KYOCERA AVX reserves the right to supply higher volage ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

Part No.	Part No. Case Size Capacitance (μF)		Rated Voltage (V)	Maximum Operating Temp. (°C)	DCL Max. (µA)	DF Max. (%)	Impedance @100kHz (Ω)	MSL
			4 V	olt				
TCA0G106M8R	Α	10	4	125	0.5	8	4.2	1
TCM0G106M8R	М	10	4	125	0.5	20	9	1
TCP0G106M8R	Р	10	4	125	0.5	20	9.3	1
TCA0G226M8R	Α	22	4	125	0.9	8	3	1
TCM0G226M8R	М	22	4	125	0.9	20	9	1
TCP0G226M8R	Р	22	4	125	0.9	20	7.7	1
TCA0G336M8R	Α	33	4	125	1.3	10	3.5	1
TCA0G476M8R	Α	47	4	125	1.9	12	3.2	1
TCA0G686M8R	Α	68	4	125	2.7	18	3	1
TCA0G107M8R	Α	100	4	125	4.0	30	3	1
TCA0G107M8R-02	Α	100	4	125	3.8	30	4	1
			6.3 \	/olt				
TCP0J225M8R	Р	2.2	6.3	125	0.5	20	17.5	1
TCA0J475M8R	Α	4.7	6.3	125	0.5	8	4.9	1
TCM0J475M8R	М	4.7	6.3	125	0.5	20	9	1
TCP0J475M8R	Р	4.7	6.3	125	0.5	20	11.8	1
TCP0J685M8R	Р	6.8	6.3	125	0.5	20	9.3	1
TCA0J106M8R	Α	10	6.3	125	0.6	8	4	1
TCM0J106M8R	М	10	6.3	125	0.6	20	9	1
TCM0J106M8R-02	М	10	6.3	125	0.6	20	9	1
TCM0J106M8R-CA2	М	10	6.3	125	0.3	20	8	1
TCP0J106M8R	Р	10	6.3	125	0.6	20	8.3	1
TCP0J106M8R-02	Р	10	6.3	125	0.1	20	6	1
TCP0J106M8R-Y1	Р	10	6.3	125	0.6	20	8.3	1
TCP0J156M8R	Р	15	6.3	125	0.9	20	7.7	1





RATINGS & PART NUMBER REFERENCE

Part No.	Case Size	Capacitance (μF)	Rated Voltage (V)	Maximum Operating Temp. (°C)	DCL Max. (μA)	DF Max. (%)	Impedance @100kHz (Ω)	MSL
TCA0J226M8R	А	22	6.3	125	1.4	10	3.5	1
TCM0J226M8R-CA2	М	22	6.3	125	6.9	20	8	1
TCM0J226M8R-EV2	M	22	6.3	125	13.0	30	9	1
TCM0J226M8R-V1	М	22	6.3	125	13.0	30	9	1
TCP0J226M8R	Р	22	6.3	125	1.4	25	5	1
TCP0J226M8R-02	Р	22	6.3	125	1.4	25	5	1
TCA0J336M8R	Α	33	6.3	125	2.1	12	3.2	1
TCA0J336M8R-E1	Α	33	6.3	125	2.1	12	3.2	1
TCM0J336M8R-V1	М	33	6.3	125	208.0	30	9	1
TCA0J476M8R	Α	47	6.3	125	3.0	18	3.2	1
TCA0J476M8R-02	Α	47	6.3	125	3.0	18	3.2	1
TCA0J476M8R-E1	А	47	6.3	125	3.0	18	3.2	1
			10 V					
TCP1A105M8R	Р	1.0	10	125	0.5	10	17.5	1
TCA1A225M8R	A	2.2	10	125	0.5	6	5.6	1
TCM1A225M8R	M	2.2	10	125	0.5	20	13.5	1
TCP1A225M8R	P	2.2	10	125	0.5	20	14.4	1
TCA1A335M8R	A	3.3	10	125	0.5	8	4.9	1
TCP1A335M8R	P	3.3	10	125	0.5	20	11.8	1
TCA1A475M8R	A	4.7	10	125	0.5	8	4.2	1
TCM1A475M8R	M	4.7	10	125	0.5	20	9	1
TCM1A475M8R-E1	M	4.7	10	125	0.5	20	9	1
TCP1A475M8R	P	4.7	10	125	0.5	20	9.3	1
TCA1A685M8R	A	6.8	10	125	0.7	8	4	1
TCA1A106*8R	A	10	10	125	1.0	8	3	1
TCM1A106M8R	M	10	10	125	10.0	20	9	1
TCM1A106M8R-02	M	10	10	125	10.0	20	9	1
TCM1A106M8R-CA2	M	10	10	125	2.0	20	8	1
TCP1A106M8R	P	10	10	125	1.0	20	7.7	1
TCP1A106M8R-02	P	10	10	125	1.0	20	7.7	1
TCA1A156M8R	A	15	10	125	1.5	10	3.5	1
TCA1A226M8R	A	22	10	125	2.2	12	3.2	1
TCA1A336M8R	A	33	10	125	3.3	8	1.7	1
TCATASSOMBIX	^		16 V		3.3	0	1.7	
TCA1C105M8R	Ι Δ	1.0	16	125	0.5	6	7	1
TCM1C105M8R	A M	1.0	16	125	0.5 0.5	10	15	<u>1</u>
TCM1C105M8R-02	M	1.0	16	125	0.5	10	15	1
TCP1C105M8R	P	1.0	16	125	0.5	10	16.1	1
	P			125		10		
TCP1C105M8R	+	1.0 1.5	16 16	125	0.5 0.5	6	16.1 5.6	1 1
TCA1C155M8R	A	2.2	16	125	0.5		4.9	
TCA1C225M8R	A M	2.2	16	125	0.5	6 20	13.5	1
TCM1C225M8R				125		20		1
TCM1C225M8R-CA2	M	2.2	16		0.5		13.5	1 1
TCA1C335M8R	A	3.3	16	125	0.5	6	4.8	
TCA1C475M8R	A	4.7	16	125	0.8	6	3.9	1
TCA1C685M8R	A	6.8	16	125	1.1	6	3.8	1
TCA1C106*8R	A	10	16	125	1.6	8	3.5	1
TCA1C106K8R-02	A	10	16	125	1.6	8	3.5	1
TCA1C106M8R-02	A	10	16	125	1.3	8	2.6	1
TCA1C226M8R	A	22	16	125	3.5	30	2.3	1
T0.14D405: :		1	20 V					
TCA1D105M8R	A	1.0	20	125	0.5	6	7	1_
TCA1D475M8R	Α	4.7	20	125	0.9	6	3.9	1
			25 V					
TCA1E105M8R	A	1.0	25	125	0.5	6	7	1
	М	1.0	25	125	0.5	10	10	1
TCM1E105M8R		1.0	25	125	0.6	20	9.3	1
TCM1E105M8R TCP1E105M8R	P	1.0						
TCM1E105M8R	P A	3.3	25	125	0.8	6	4.8	1
TCM1E105M8R TCP1E105M8R							4.8 3.4	1 1
TCM1E105M8R TCP1E105M8R TCA1E335M8R	A	3.3	25	125 125	0.8	6		

Moisture Sensitivity Level (MSL) is defined according to J-STD-020. All technical data relates to an ambient temperature of +25C.

Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 1.5 volts.

DCL is measured at rated voltage after 5 minutes.

Impedance allowed to move up to 1.25 times catalog limit post mounting.

 $NOTE: KYOCERA\ AVX\ reserves\ the\ rights\ to\ supply\ higher\ voltage\ rating\ in\ the\ same\ case\ size,\ to\ the\ same\ reliability\ standards.$








QUALIFICATION TABLE

TECT	TC series (Temperature range -55°C to +125°C)								
TEST		Condition		Characteristics					
	Apply rated volta	ge (Ur) at 85°C for	1000hrs (for M	Visual examination	no visible damage				
		hrs (for A case) th		DCL	2x initial limit				
Endurance		0Ω. Stabilize at roo		ΔC/C	within ±30% of initi	al value (M case), ±	20% (A,P case)		
	for 24 hours befo	ore measuring.		DF	2x initial limit				
				Visual examination	no visible damage				
		90-95% relative hur	,	DCL	2x initial limit				
Humidity		ilize at room tempe		ΔC/C	within ±30% of initial value (M case), ±20% (A,P case				
	numidity for 24 h	ours before measu	iring.	DF	2x initial limit				
	Step	Temperature°C	Duration(min)		-55°C	+85°C	+125°C		
	1	-55	15	<u> </u>					
Temperature	2	+85	15	DCL	n/a	10xIL*	12.5xIL*		
Stability	3	+125	15	ΔC/C	0/-30%	+15/-5%	+20/-5%		
				DF	IL*	IL*	IL*		
	Apply 1 2y rated	voltago (Ur) at 95±	2°C for	Visual examination	no visible damage				
Surge Voltage	Apply 1.3x rated voltage (Ur) at 85±2°C for 1000 cycles, 300sec charge and 30sec discharge			DCL	2x initial limit				
Surge voltage	resistance 10000	Ω.		ΔC/C	±20% of initial limit	±20% of initial limit			
				DF	2x initial limit				
	4.17 JIS C 5101-	1		Visual examination	no visible damage				
Vihuatian	Frequency: 10 to	55 to 10Hz/min.		DCL	initial limit				
Vibration	Amplitude: 1.5mi	m		ΔC/C	within ± 5% of initia	within ± 5% of initial value			
	Time: 2hours eac	h in X and Y directi	ions	DF	initial limit				

^{*}Initial Limit

For use outside of recommended conditions and special request, please contact KYOCERA AVX. Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.

PACKAGING SPECIFICATIONS



Unit (mm)

Case	A±0.10	B±0.10	W±0.20	E±0.10	F±0.05	P1±0.10	P2±0.05	PO±0.10	DO+0.10/0	t1±0.05	t2±0.10	Standard packaging quantity
Α	1.90	3.50	8.00	1.75	3.50	4.00	2.00	4.00	φ1.50	0.25	1.90	2,000 pcs
М	1.00	1.85	8.00	1.75	3.50	4.00	2.00	4.00	φ1.50	0.20	1.00	4,000 pcs
Р	1.55	2.30	8.00	1.75	3.50	4.00	2.00	4.00	φ1.55±0.05	0.25	1.32	3,000 pcs

REEL DIMENSIONS

